



Coil Hook Type CKPM

Product information



Counterbalanced

General: For medium and large loads and coil widths. A separate stand should be used for the coil when it is discharged. See the introductory text above in the section on C-hooks.

Design: Low profile where there is limited headroom. The counterbalance ensures that the fork is always in a horizontal position, regardless of whether the hook is empty or loaded. Arched plate on top section helps to protect the coils.

Proof: 1,5 x WLL.

Material: Plate of high-strength structural steel.

Marking: Type, working load limit, maximum coil width and CE marking.

Finish: Yellow painted.

Note: We recommend the use of a 2-leg chain sling, headroom permitting as an increase in dimension L provides better balance.

Safety factor: 1,5 x WLL.

Part code	WLL ton	Max coil width mm	B mm	C mm	E mm	G mm	H mm	L mm	S mm	Weight kg	Delivery time
503500507500060	5	750	90	200	565	80	550	380	170	225	7
503501001270060	10	1,270	90	200	1,270	100	700	475	250	630	7
503501001500060	10	1,500	90	200	1,100	100	650	500	290	910	7
503501206000060	12	600	120	250	600	100	900	500	235	430	7
503501501700060	15	1,700	140	300	1,300	100	700	660	350	1,060	7
503502001500060	20	1,500	140	300	1,125	110	770	680	365	1,300	7
503502501350060	25	1,350	200	400	1,015	120	900	780	365	1,400	7
503503001500060	30	1,500	200	400	1,125	120	1,000	820	400	1,900	7

Blueprint

